



	6 inch-Low \$		6 inch		8 inch		10 inch		12 inch		15 inch	
	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9
Resolution	320x240		320x240		640x480	800x600	640x480	800x600	800x600		1024x768	
Cutout	same		same		same		same		same		same	
Footprint	same		same			Smaller		Smaller		Smaller		Smaller
Bezel Label	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES
Power LED	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES
User LED	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES	NA	YES
Backlight	CCFL/LED	LED	CCFL/LED	LED	CCFL/LED	LED	CCFL/LED	LED	CCFL/LED	LED	CCFL/LED	LED
Speed (MHz)	333	800	400	800	400	800	400	800	400	800	400	800
Flash Mem	32MB	128MB	32MB	128MB	32MB	128MB	32MB	128MB	64MB	128MB	64MB	128MB
SDRAM	32MB	128MB	32MB	128MB	32MB	128MB	32MB	128MB	64MB	256MB	64MB	256MB
Retent. Mem.	256K	512K	256K	512K	256K	512K	256K	512K	256K	512K	256K	512K
Mem Backup	Battery	S-Cap	Battery	S-Cap	Battery	S-Cap	Battery	S-Cap	Battery	S-Cap	Battery	S-Cap
Project Mem	10MB	26MB	10MB	26MB	10MB	26MB	10MB	26MB	40MB	82MB	40MB	82MB
Calendar	YES		YES		YES		YES		YES		YES	
USB	1.1	2.0	1.1	2.0	1.1	2.0	1.1	2.0	1.1	2.0	1.1	2.0
Ethernet	NA	NA	10/100	Auto-X	10/100	Auto-X	10/100	Auto-X	10/100	Auto-X	10/100	Auto-X
Mouse	NO	YES	NO	YES	NO	YES	NO	YES	NO	YES	NO	YES
Serial Ports	1	1	1	3	1	3	1	3	1	3	1	3
Ext Memory	NA	SD	CF	SD	CF	SD	CF	SD	CF	2-SD	CF	2-SD
Opt Module	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.
Video Out	NA	NA	NA	NA	NA	NA	NA	NA	NA	HDMI	NA	HDMI
Power	24Vdc	12/24Vdc	24Vdc	12/24Vdc	24Vdc	12/24Vdc	24Vdc	12/24Vdc	24Vdc	12/24Vdc	24Vdc	12/24Vdc
EA-AC	YES		YES		YES		YES		YES		YES	
UL	YES		YES		YES		YES		YES		YES	
cUL	YES		YES		YES		YES		YES		YES	
CSA	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.
Symbols		+1000		+1000		+1000		+1000		+1000		+1000
Software	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9	EA7	EA9
Manual	online	online	online	online	online	online	online	online	online	online	online	online
EZTouch	Import	n.a.	Import	n.a.	Import	n.a.	Import	n.a.	Import	n.a.	Import	n.a.
Mic-in	YES		YES		YES		YES		YES		YES	
Audio Out	YES		YES		YES		YES		YES		YES	
Monochrome	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.	YES	n.a.
Price	\$540	\$499	\$757	\$699	\$1081	\$999	\$1727	\$1290	\$2051	\$1790	\$2484	\$1999